



Miniature, Multi-Position Fixed PCB Terminal Blocks

The CPA is a single sub-miniature printed circuit board terminal block that is available in several pin spacings and from 1 to 24 positions. The CPA uses a moving metal body design for the termination of the wire to insure maximum reliability. The CPA is UL recognized and will terminate wire ranging from 16 to 30 A WG and will handle 10 amps at 300 volts. The CPA is available in a right angle version. The standard color is green, however several other colors are available upon request.

SPECIFICATIONS

Housing Material:	PA68 Polyamide, Flammable UL94V0
Housing Color:	Green
Screw:	Zinc Plated Steel
Clamp:	Nickel Plated Brass
Pin:	Tin Plated Brass
Testing torque:	2.7 in/lb
Wire range:	16-30 AWG
P.C.B. mounting hole:	1.1mm
Nominal current:	10 A
Voltage:	300 V
Temperature Range:	-30° C to 110° C



Catalog #	No. of Positions	Length (mm)
CPA3.5-2VE	2	7
CPA3.5-3VE	3	10.5
CPA3.5-4VE	4	14
CPA3.5-5VE	5	18.5
CPA3.5-6VE	6	21
CPA3.5-7VE	7	24.5
CPA3.5-8VE	8	28
CPA3.5-9VE	9	31.5
CPA3.5-10VE	10	35
CPA3.5-11VE	11	38.5
CPA3.5-12VE	12	42
CPA3.5-13VE	13	45.5
CPA3.5-14VE	14	49
CPA3.5-15VE	15	52.5
CPA3.5-16VE	16	56
CPA3.5-17VE	17	59.5
CPA3.5-18VE	18	63
CPA3.5-19VE	19	66.5
CPA3.5-20VE	20	70
CPA3.5-21VE	21	73.5
CPA3.5-22VE	22	77
CPA3.5-23VE	23	80.5
CPA3.5-24VE	24	84