


Certifications	
	
Material	
Pin/Plate	Copper Alloy
Housing	PA, UL94V-0
Electrical	
Rated Voltage [V]	320
Rated Current [A]	7
Mechanical	
Temperature Range [C]	-55 ~+160
Wire Range	20 - 12
Size	
Pitch	5.0
Poles	2-24

Item	Positions	Length (mm)
CPF5-2VE	2	10
CPF5-3VE	3	15
CPF5-4VE	4	20
CPF5-5VE	5	25
CPF5-6VE	6	30
CPF5-7VE	7	35
CPF5-8VE	8	40
CPF5-9VE	9	45
CPF5-10VE	10	50
CPF5-11VE	11	55
CPF5-12VE	12	60
CPF5-13VE	13	65
CPF5-14VE	14	70
CPF5-15VE	15	75
CPF5-16VE	16	80
CPF5-17VE	17	85
CPF5-18VE	18	90
CPF5-19VE	19	95
CPF5-20VE	20	100
CPF5-21VE	21	105
CPF5-22VE	22	110
CPF5-23VE	23	115
CPF5-24VE	24	120