


Certifications	
	
Material	
Pin/Plate	Copper Alloy
Housing	PA, UL94V-0
Electrical	
Rated Voltage [V]	320
Rated Current [A]	7
Mechanical	
Temperature Range [C]	-55 ~+160
Wire Range	20 - 12
Size	
Pitch	5.08
Poles	2-24

Item	Positions	Length (mm)
CPF5.08-2VE	2	10.16
CPF5.08-3VE	3	15.24
CPF5.08-4VE	4	20.32
CPF5.08-5VE	5	25.4
CPF5.08-6VE	6	30.48
CPF5.08-7VE	7	35.56
CPF5.08-8VE	8	40.64
CPF5.08-9VE	9	45.72
CPF5.08-10VE	10	50.8
CPF5.08-11VE	11	55.88
CPF5.08-12VE	12	60.96
CPF5.08-13VE	13	66.04
CPF5.08-14VE	14	71.12
CPF5.08-15VE	15	76.2
CPF5.08-16VE	16	81.28
CPF5.08-17VE	17	86.36
CPF5.08-18VE	18	91.44
CPF5.08-19VE	19	96.52
CPF5.08-20VE	20	101.6
CPF5.08-21VE	21	106.68
CPF5.08-22VE	22	111.76
CPF5.08-23VE	23	116.84
CPF5.08-24VE	24	121.92