

5.08mm Pluggable Terminal Blocks

SPECIFICATIONS

Housing Material:	PA68 Polyamide, Flammable UL94V0
Housing Color:	Green
Screw:	Zinc Plated Steel
Clamp:	Nickel Plated Brass
Pin:	Tin Plated Brass
Testing torque:	4.4 in/lb.
Wire range:	12-24 AWG
Nominal current:	12 A
Voltage:	300 V
Temperature Range:	-30° C to 85° C



Part# #of Positions

CPF5.08-2FV	2
CPF5.08-3FV	3
CPF5.08-4FV	4
CPF5.08-5FV	5
CPF5.08-6FV	6
CPF5.08-7FV	7
CPF5.08-8FV	8
CPF5.08-9FV	9
CPF5.08-10FV	10
CPF5.08-11FV	11
CPF5.08-12FV	12
CPF5.08-13FV	13
CPF5.08-14FV	14
CPF5.08-15FV	15
CPF5.08-16FV	16
CPF5.08-17FV	17
CPF5.08-18FV	18
CPF5.08-19FV	19
CPF5.08-20FV	20
CPF5.08-21FV	21
CPF5.08-22FV	22
CPF5.08-23FV	23
CPF5.08-24FV	24

