

5mm Pluggable Terminal Blocks

SPECIFICATIONS

Housing Material:	PA68 Polyamide, Flammable UL94V0
Housing Color:	Green
Screw:	Zinc Plated Steel
Clamp:	Nickel Plated Brass
Pin:	Tin Plated Brass
Testing torque:	4.4 in/lb.
Wire range:	12-24 AWG
Nominal current:	12 A
Voltage:	300 V
Temperature Range:	-30° C to 85° C



Part# #of Positions

CPF5-2FV	2
CPF5-3FV	3
CPF5-4FV	4
CPF5-5FV	5
CPF5-6FV	6
CPF5-7FV	7
CPF5-8FV	8
CPF5-9FV	9
CPF5-10FV	10
CPF5-11FV	11
CPF5-12FV	12
CPF5-13FV	13
CPF5-14FV	14
CPF5-15FV	15
CPF5-16FV	16
CPF5-17FV	17
CPF5-18FV	18
CPF5-19FV	19
CPF5-20FV	20
CPF5-21FV	21
CPF5-22FV	22
CPF5-23FV	23
CPF5-24FV	24

