

The ASI miniature terminal blocks mount on the 15mm DIN rail and are ideal for applications using small enclosures or where space is available to be used with these popular miniature terminal blocks making them versatile for just about any type of application.



Terminal Width 5.2mm
ASIMBK3EZ



Terminal Width 6.2mm
ASIMBK5EZ



Terminal Width 8.2mm
ASIMBK6E

SPECIFICATIONS

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
Wire range, AWG	28-12	26-10	26-8
Current Rating	20	30	50
Voltage Rating	300	300	300
Dimensions (L x H) mm	28 x 31	28 x 31	35 x 35.2

ORDERING INFORMATION

	ORDER #	PCS/ PKG	ORDER #	PCS/ PKG	ORDER #	PCS/ PKG
Terminal Block	ASIMBK3EZ	50	ASIMBK5EZ	50	ASIMBK6E	50

ACCESSORIES

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
End Cover	ASIDMBKE	25 ASIDMBKE	25 ASIDMBK6E
Separating Plate	ASITSKK3	25 ASITSKK3	25 ASITSKK3
Partition Plate	ASIATPMBK	25 ASIATPMBK	25 ASIATPMBK

CIRCUIT BRIDGES

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
Internal 10 position (With Screws)	ASIFBRNI105N	10 ASIFBNI106	10 ASIFBNI108
External 2 position		ASIEB26	25 ASIEB28
3 position		ASIEB36	25 ASIEB38
10 position	ASIEBL105	10 ASIEB106	10 ASIEB108

TB MARKERS

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
Blank	ASIZB510B	10 ASIZB610B	10 ASIZB810B
Pre-printed 1-10 vert.	ASIZB51010V	10 ASIZB61010V	10 ASIZB81010V
Pre-printed 1-10 horz.	ASIZB51010H	10 ASIZB61010H	10 ASIZB81010H
Custom	ASIZB5CXXX	- ASIZB6CXXX	- ASIZB8CXXX

END STOP

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
(snap-on)	ASIEMK1	25 ASIEMK1	25 ASIEMK1

DIN RAIL

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
(2 meters)			
15mm slotted	PR010	1 PR010	1 PR010
15mm non-slotted	PR009	1 PR009	1 PR009

SCREWDRIVER

	ASIMBK3EZ	ASIMBK5EZ	ASIMBK6E
	CCV05	1 CCV05	1 CCV05
		CCH06	1 CCH06