

The MRT18 printed circuit board terminal blocks are one-piece modular units in sizes of 2 and 3 circuits. The standard size block has a UL rating of 20 amps, 300 volts, and can handle wires of 12 to 30 AWG. The moving metal body design ensures maximum wire termination reliability. The standard color of the MRT18 is green, however other colors are available upon request.

SPECIFICATIONS

Housing Material:	PA68 Polyamide, Flammable UL94V0
Housing Color:	Green
Screw:	Zinc Plated Steel
Clamp:	Nickel Plated Brass
Pin:	Tin Plated Brass
Testing torque:	4.4 in/lb
Wire range:	12-30 AWG
P.C.B. mounting hole:	1.5mm
Nominal current:	20 A
Voltage:	300 V
Temperature Range:	-30° C to 110° C



Catalog #	Positions	Length (mm)
MRT18P5.08-2V07VE	2	10.16
MRT18P5.08-3V07VE	3	15.24

