

High Current Panel and Rack Mount Magnetic Circuit Breakers

The NDB3-100 series is a panel or rack mount circuit breaker family. The robust line can be screw, snap-in or plug mounted. The NDB3-100 is available in one; two or three pole, 1 to 100 amps, and with short, medium and long delay AC or DC trip curves. The easy to read printing can be specified in either the vertical or the horizontal position.



One Pole



Two Pole



Three Pole

Features:

- UL489A Listed
- AC and DC operation
- Screw, snap-in or plug mounted
- 1 to 100 amp ratings
- ROHS Compliant
- Easy to read printing

Provide protection for:

- Telecommunications
- Railway locomotive
- Medical Equipment
- UPS Equipment

DC Medium Delay Trip Curve

Rated Current (Amps)	One Pole	Two Pole	Three Pole
1	NDB3-100Z41-1LSS1A0L	NDB3-100Z41-2LSS1A0L	NDB3-100Z41-3LSS1A0L
2	NDB3-100Z42-1LSS1A0L	NDB3-100Z42-2LSS1A0L	NDB3-100Z42-3LSS1A0L
3	NDB3-100Z43-1LSS1A0L	NDB3-100Z43-2LSS1A0L	NDB3-100Z43-3LSS1A0L
4	NDB3-100Z44-1LSS1A0L	NDB3-100Z44-2LSS1A0L	NDB3-100Z44-3LSS1A0L
5	NDB3-100Z45-1LSS1A0L	NDB3-100Z45-2LSS1A0L	NDB3-100Z45-3LSS1A0L
6	NDB3-100Z46-1LSS1A0L	NDB3-100Z46-2LSS1A0L	NDB3-100Z46-3LSS1A0L
8	NDB3-100Z48-1LSS1A0L	NDB3-100Z48-2LSS1A0L	NDB3-100Z48-3LSS1A0L
10	NDB3-100Z410-1LSS1A0L	NDB3-100Z410-2LSS1A0L	NDB3-100Z410-3LSS1A0L
12	NDB3-100Z412-1LSS1A0L	NDB3-100Z412-2LSS1A0L	NDB3-100Z412-3LSS1A0L
15	NDB3-100Z415-1LSS1A0L	NDB3-100Z415-2LSS1A0L	NDB3-100Z415-3LSS1A0L
16	NDB3-100Z416-1LSS1A0L	NDB3-100Z416-2LSS1A0L	NDB3-100Z416-3LSS1A0L
20	NDB3-100Z420-1LSS1A0L	NDB3-100Z420-2LSS1A0L	NDB3-100Z420-3LSS1A0L
24	NDB3-100Z424-1LSS1A0L	NDB3-100Z424-2LSS1A0L	NDB3-100Z424-3LSS1A0L
25	NDB3-100Z425-1LSS1A0L	NDB3-100Z425-2LSS1A0L	NDB3-100Z425-3LSS1A0L
30	NDB3-100Z430-1LSS1A0L	NDB3-100Z430-2LSS1A0L	NDB3-100Z430-3LSS1A0L
35	NDB3-100Z435-1LSS1A0L	NDB3-100Z435-2LSS1A0L	NDB3-100Z435-3LSS1A0L
40	NDB3-100Z440-1LSS1A0L	NDB3-100Z440-2LSS1A0L	NDB3-100Z440-3LSS1A0L
45	NDB3-100Z445-1LSS1A0L	NDB3-100Z445-2LSS1A0L	NDB3-100Z445-3LSS1A0L
50	NDB3-100Z450-1LSS1A0L	NDB3-100Z450-2LSS1A0L	NDB3-100Z450-3LSS1A0L
60	NDB3-100Z460-1LSS1A0L	NDB3-100Z460-2LSS1A0L	NDB3-100Z460-3LSS1A0L
70	NDB3-100Z470-1LSS1A0L	NDB3-100Z470-2LSS1A0L	NDB3-100Z470-3LSS1A0L
80	NDB3-100Z480-1LSS1A0L	NDB3-100Z480-2LSS1A0L	NDB3-100Z480-3LSS1A0L
90	NDB3-100Z490-1LSS1A0L	NDB3-100Z490-2LSS1A0L	NDB3-100Z490-3LSS1A0L
100	NDB3-100Z4100-1LSS1A0L	NDB3-100Z4100-2LSS1A0L	NDB3-100Z4100-3LSS1A0L

Specifications

Number of Poles: 1, 2 & 3
 Rated Voltage: AC 230/400
 DC 80
 Min. Amp Rating: 1A
 Max. Amp Rating: 100A
 Interrupting Capacity: 4kA
 Mechanical Life: 10,000 Operations
 Operating Temp. Range: -40°C - 85°C
 Agency Approvals: UL489A, CE, TUV, ROHS

