

## Snap-In Panel Mount Hydraulic Magnetic Circuit Breaker



### Features:

- UL1077 Listed
- Easy snap-in mounting
- Short and Medium trip curves
- 1 to 30 amp ratings
- Rocker guard standard
- Black, white or orange rockers
- Easy to read printing
- RoHs compliant

### Provide protection for:

- Power Supplies
- Office Equipment
- Medical Equipment
- Vending Machines
- Amusement Equipment
- Fitness Equipment
- Telecommunications

### Specifications:

Number of Poles	1
Rated Voltage	AC 250V, DC 80V
Min. Amp Rating	1A
Max. Amp Rating	30A
Interrupting Capacity	1.0kA
Mechanical Life	10,000 Operations
Operating Temp. Range	-40°C - 85°C
Agency Approvals	UL1077, TUV

### DC Medium Delay Trip Curve

Rated Current (Amps)	Part Number
1	NDB3-30Z41-1QHY110R
2	NDB3-30Z42-1QHY110R
3	NDB3-30Z43-1QHY110R
4	NDB3-30Z44-1QHY110R
5	NDB3-30Z45-1QHY110R
6	NDB3-30Z46-1QHY110R
8	NDB3-30Z48-1QHY110R
10	NDB3-30Z410-1QHY110R
12	NDB3-30Z412-1QHY110R
15	NDB3-30Z415-1QHY110R
16	NDB3-30Z416-1QHY110R
20	NDB3-30Z420-1QHY110R
24	NDB3-30Z424-1QHY110R
25	NDB3-30Z425-1QHY110R
30	NDB3-30Z430-1QHY110R

### AC Medium Delay Trip Curve

Rated Current (Amps)	Part Number
1	NDB3-30J41-1QHY110R
2	NDB3-30J42-1QHY110R
3	NDB3-30J43-1QHY110R
4	NDB3-30J44-1QHY110R
5	NDB3-30J45-1QHY110R
6	NDB3-30J46-1QHY110R
8	NDB3-30J48-1QHY110R
10	NDB3-30J410-1QHY110R
12	NDB3-30J412-1QHY110R
15	NDB3-30J415-1QHY110R
16	NDB3-30J416-1QHY110R
20	NDB3-30J420-1QHY110R
24	NDB3-30J424-1QHY110R
25	NDB3-30J425-1QHY110R
30	NDB3-30J430-1QHY110R

\*Other amperages available upon request

