


| Certification | |
|---|--|
|  | |
| Material | |
| Screw Lock | M3.0 Steel, Zinc Plated |
| Screw | M3.0 Steel, Zinc Plated |
| Contact | Copper Alloy, Nickel + Tin Plated |
| Cage | Copper Alloy, Nickel Plated |
| Housing | PA 66 M3.0 Steel, Zinc Plated, UL 94V-0, Green |
| Electrical | |
| Standard | UL 1059/CSA C22.2 No. 158 |
| Rated Voltage | 600 V |
| Rated Current | 41 A |
| Wire Range | 24-8 AWG |
| Mechanical | |
| Temperature Range | -40°C...+130°C |
| Torque | 0.7N-m (6.2lb-in) |
| Strip Length | 10 mm (0.39") |
| Size | |
| Pitch | 7.62 mm (.300") |
| Poles | 2P-12P. Additional sizes available on request. |

| Item | No. of Poles | Length (mm) |
|------------------|--------------|-------------|
| PWF1P-7.62-2FV | 2 | 30.48 |
| PWF1P-7.62-3FV | 3 | 38.1 |
| PWF1P-7.62-4FV | 4 | 45.72 |
| PWF1P-7.62-5FV | 5 | 53.34 |
| PWF1P-7.62-6FV | 6 | 60.96 |
| PWF1P-7.62-7FV | 7 | 68.58 |
| PWF1P-7.62-8FV | 8 | 76.2 |
| PWF1P-7.62-9FV | 9 | 83.82 |
| PWF1P-7.62-10FV | 10 | 91.44 |
| PWF1P-7.62-11FV | 11 | 99.06 |
| PWF1P-7.62-12PFV | 12 | 106.68 |