



Certification	
Material	
Header Pin	Copper Alloy, Tin Plated
Housing	PA 66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V UGC, 600 V UGD
Rated Current	41 A
Mechanical	
Temperature Range	-40°C...+130°C
Size	
Pitch	7.62 mm (.300")
Poles	2P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
PWM1P-7.62-2DP	2	15.24
PWM1P-7.62-3DP	3	22.86
PWM1P-7.62-4DP	4	30.48
PWM1P-7.62-5DP	5	38.1
PWM1P-7.62-6DP	6	45.72
PWM1P-7.62-7DP	7	53.34
PWM1P-7.62-8DP	8	60.96
PWM1P-7.62-9DP	9	68.58
PWM1P-7.62-10DP	10	76.2
PWM1P-7.62-11DP	11	83.82
PWM1P-7.62-12DP	12	91.44