



Certification	
	<b>UL</b> <sup>®</sup> <b>US</b>
Material	
Header Pin	Copper Alloy, Tin Plated
Housing	PA 66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V UGC, 600 V UGD
Rated Current	41 A
Mechanical	
Temperature Range	-40°C...+130°C
Size	
Pitch	7.62 mm (.300")
Poles	2P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
PWM1P-7.62-2DPSQ	2	15.24
PWM1P-7.62-3DPSQ	3	22.86
PWM1P-7.62-4DPSQ	4	30.48
PWM1P-7.62-5DPSQ	5	38.1
PWM1P-7.62-6DPSQ	6	45.72
PWM1P-7.62-7DPSQ	7	53.34
PWM1P-7.62-8DPSQ	8	60.96
PWM1P-7.62-9DPSQ	9	68.58
PWM1P-7.62-10DPSQ	10	76.2
PWM1P-7.62-11DPSQ	11	83.82
PWM1P-7.62-12DPSQ	12	91.44