


Certification	
	
Material	
Screw	M4.0 Copper Alloy, Nickel Plated
Contact	Copper Alloy, Nickel + Tin Plated
Cage	Copper Alloy, Nickel Plated
Housing	PA G, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	60 A
Wire Range	20-6 AWG
Mechanical	
Temperature Range	-40°C...+130°C
Torque	1.2N-m (14lb-in)
Strip Length	10 mm (0.39")
Size	
Pitch	10.16 mm (.400")
Poles	1P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
PWT1P-10.16-2BF	2	20.32
PWT1P-10.16-3BF	3	30.48
PWT1P-10.16-4BF	4	40.64
PWT1P-10.16-5BF	5	50.8
PWT1P-10.16-6BF	6	60.96
PWT1P-10.16-7BF	7	71.12
PWT1P-10.16-8BF	8	81.28
PWT1P-10.16-9BF	9	91.44
PWT1P-10.16-10BF	10	101.6
PWT1P-10.16-11BF	11	111.76
PWT1P-10.16-12BF	12	121.92