

## Transparent sleeves for rigid cable tags

Transparent PVC sleeve, width 4 mm, available in lengths from 12 to 23 mm, for use with **NUT** series tags. Appropriate for identification of wire sections, from a minimum 0.22 mm<sup>2</sup> up to a maximum of 35 mm<sup>2</sup>.

- Material: PVC (polyvinyl chloride)
- Self-extinguishing: UL94-V0
- Working temperature: -40°/+80°C



TUB12



TUB15



TUB18



TUB23

| CODE    | ID CODE | DESCRIPTION        | SIZE IN mm |       | WIRE SECTION                 | CABLE DIAMETER         | PIECES PK. |
|---------|---------|--------------------|------------|-------|------------------------------|------------------------|------------|
|         |         |                    | LENGTH     | WIDTH | MIN - MAX IN mm <sup>2</sup> | MIN - MAX IN mm        |            |
|         |         |                    |            |       | APPROXIMATE                  |                        |            |
| TUB1200 | TUB1200 | transparent sleeve | 12         | 4     | 0.22 - 0.5 mm <sup>2</sup>   | from 1 mm to 2 mm      | 1,000      |
| TUB1201 | TUB1201 | transparent sleeve | 12         | 4     | 0.5 - 1.5 mm <sup>2</sup>    | from 1.8 mm to 2.5 mm  | 3,000      |
| TUB1202 | TUB1202 | transparent sleeve | 12         | 4     | 0.5 - 2.5 mm <sup>2</sup>    | from 2 mm to 4.1 mm    | 3,000      |
| TUB1203 | TUB1203 | transparent sleeve | 12         | 4     | 2.5 - 10 mm <sup>2</sup>     | from 4 mm to 6.8 mm    | 1,000      |
| TUB1204 | TUB1204 | transparent sleeve | 12         | 4     | 2.5 - 16 mm <sup>2</sup>     | from 6 mm to 9.5 mm    | 500        |
| TUB1205 | TUB1205 | transparent sleeve | 12         | 4     | 4.0 - 35 mm <sup>2</sup>     | from 9.6 mm to 13.5 mm | 500        |
| TUB1500 | TUB1500 | transparent sleeve | 15         | 4     | 0.22 - 0.5 mm <sup>2</sup>   | from 1 mm to 2 mm      | 1,000      |
| TUB1501 | TUB1501 | transparent sleeve | 15         | 4     | 0.5 - 1.5 mm <sup>2</sup>    | from 1.8 mm to 2.5 mm  | 3,000      |
| TUB1502 | TUB1502 | transparent sleeve | 15         | 4     | 0.5 - 2.5 mm <sup>2</sup>    | from 2 mm to 4.1 mm    | 3,000      |
| TUB1503 | TUB1503 | transparent sleeve | 15         | 4     | 2.5 - 10 mm <sup>2</sup>     | from 4 mm to 6.8 mm    | 1,000      |
| TUB1504 | TUB1504 | transparent sleeve | 15         | 4     | 2.5 - 16 mm <sup>2</sup>     | from 6 mm to 9.5 mm    | 500        |
| TUB1505 | TUB1505 | transparent sleeve | 15         | 4     | 4.0 - 35 mm <sup>2</sup>     | from 9.6 mm to 13.5 mm | 500        |
| TUB1800 | TUB1800 | transparent sleeve | 18         | 4     | 0.22 - 0.5 mm <sup>2</sup>   | from 1 mm to 2 mm      | 1,000      |
| TUB1801 | TUB1801 | transparent sleeve | 18         | 4     | 0.5 - 1.5 mm <sup>2</sup>    | from 1.8 mm to 2.5 mm  | 3,000      |
| TUB1802 | TUB1802 | transparent sleeve | 18         | 4     | 0.5 - 2.5 mm <sup>2</sup>    | from 2 mm to 4.1 mm    | 3,000      |
| TUB1803 | TUB1803 | transparent sleeve | 18         | 4     | 2.5 - 10 mm <sup>2</sup>     | from 4 mm to 6.8 mm    | 1,000      |
| TUB1804 | TUB1804 | transparent sleeve | 18         | 4     | 2.5 - 16 mm <sup>2</sup>     | from 6 mm to 9.5 mm    | 500        |
| TUB1805 | TUB1805 | transparent sleeve | 18         | 4     | 4.0 - 35 mm <sup>2</sup>     | from 9.6 mm to 13.5 mm | 500        |
| TUB2300 | TUB2300 | transparent sleeve | 23         | 4     | 0.22 - 0.5 mm <sup>2</sup>   | from 1 mm to 2 mm      | 1,000      |
| TUB2301 | TUB2301 | transparent sleeve | 23         | 4     | 0.5 - 1.5 mm <sup>2</sup>    | from 1.8 mm to 2.5 mm  | 3,000      |
| TUB2302 | TUB2302 | transparent sleeve | 23         | 4     | 0.5 - 2.5 mm <sup>2</sup>    | from 2 mm to 4.1 mm    | 3,000      |
| TUB2303 | TUB2303 | transparent sleeve | 23         | 4     | 2.5 - 10 mm <sup>2</sup>     | from 4 mm to 6.8 mm    | 1,000      |
| TUB2304 | TUB2304 | transparent sleeve | 23         | 4     | 2.5 - 16 mm <sup>2</sup>     | from 6 mm to 9.5 mm    | 500        |
| TUB2305 | TUB2305 | transparent sleeve | 23         | 4     | 4.0 - 35 mm <sup>2</sup>     | from 9.6 mm to 13.5 mm | 500        |

ATTENTION: to ensure selection of the correct sleeve, use the column "cable diameter"; the column "cable section" is approximate and changes from one manufacturer to another.