




  
 CERTIFIED DIMENSIONS  
 THREE PHASE 145-750 KVA  
 NEMA II  
 DRIVE ISOLATION TRANSFORMERS

**BOTTOM**  
(145, 175, AND 330 THRU 660 KVA)



**BOTTOM**  
(220-275 KVA)



KEY:  DENOTES CONDUIT AREAS

KVA	OUTLINE/MOUNTING DIMENSIONS					SIDE VIEWS (175-750 KVA)				BOTTOM VIEWS (175-750 KVA)			
	A	B	C	D	E	X1	X2	Y1	Y2	X1	X2	Y1	Y2
145/175	42.00	40.00	30.00	37.50	19.25	—	—	—	—	12.00	—	4.00	26.00
220	54.00	45.00	30.00	29.00	21.25	8.00	22.00	24.00	44.00	8.00	22.00	13.50	31.50
275 *	56.00	48.00	40.00	39.50	31.25	10.00	30.00	26.00	46.00	10.00	30.00	14.75	32.00
330	56.00	56.00	40.50	39.50	31.25	—	—	—	42.00	—	—	—	27.50
440 & 450	62.00	54.00	41.00	38.50	33.75	13.50	—	—	50.00	13.50	—	9.00	26.50
550	—	60.00	41.50	42.50	—	—	—	4.00	—	—	—	—	31.50
660	64.00	64.00	42.50	46.50	33.25	14.50	—	—	48.00	14.50	—	15.00	27.00
750	62.80	70.50	43.50	43.00	31.50	7.00	—	6.50	21.50	—	—	6.50	21.50

\* TYPE NUMBER DMGB-275-4S "D" DIMENSION IS 40.50 INCHES.



4815 West Fifth Street  
 Lumberton, NC 28358  
 910-738-1121 Inside NC  
 800-334-5214 Outside NC  
 910-739-0024 Fax  
[www.acmepowerdist.com](http://www.acmepowerdist.com)