

# REGULATED LINEAR POWER SUPPLIES

## SPW SERIES 15 Watts to 175 Watts



CATALOG NO.	OUTPUT 1	
	VDC	AMPS
SPWS-53-OV	5	3.0
SPWS-1217	12	1.7
SPWS-2412	24	1.2
SPWS-2424	24	2.4
SPWS-2436	24	3.6
SPWS-2448	24	4.8
SPWS-2472	24	7.2

### Features

- Worldwide AC input range
- Worldwide safety standards
- Industry standard package
- Built-in OVP on 5V output
- Optional OVP for other outputs
- Overload protection with automatic recovery
- 100% burn-in
- Recognized to UL, CSA Certified, and CE Listed

### Applications

- Personal Computers
- Instrumentation
- Control Concepts
- Data Processing
- Microprocessor Circuits
- Electronic Circuits



### SPW Series Electrical Specifications

#### AC INPUT

- INPUT VOLTAGE: 100/120/220/230/240 selectable  
INPUT FREQUENCY: 47 to 63 Hz typical 60 Hz;

#### DC OUTPUT

- OUTPUT ADJUSTMENT RANGE:  $\pm 5\%$ , Min.