



Representative

**Catalog Number:** AL16/PG16/A/GR  
**Product ID:** 7TCA296000R0464  
**EAN Number:** 05020963005039  
**Status:** Active

Straight Conduit Fitting, Swivel External Male Thread, Nominal Conduit Size 16mm, PG16 Thread, Polyamide (Nylon) 66, Grey

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 16mm
Material	Polyamide/Nylon 6.6
Color	Gray
Connection	Straight
Cable Entry	PG16 Thread

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	16mm
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	Y
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	PG16
Thread length	11.5mm
Total length	26.8mm
Total height	44.5mm
Material	Polyamide
Colour	Grey
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.02 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)