



Representative

Catalog Number: AL16/U094/C90/000620
Product ID: 7TCA296000R0498
EAN Number: 05020963035937
Status: Active

Connector Conduit Fitting, 90 Degree Elbow, Conduit Size 16, 15/16 Inch Connector UNEF Thread, Swivel Internal Thread, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with UNEF Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 16mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	90 Degree
Cable Entry	15/16 Inch UNEF Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	16mm
Degree of protection (IP)	IP68
Model	90°-elbow
Revolving thread	Y
Construction type	Internal thread
Type of connection	Snap connection
Thread type	UNEF
Thread connection size	Other
Thread length	9.5mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Inner Quantity	10
Outer Quantity	250
Outer Dimensions (inches)	14x14x6
Weight Uom	0.04 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com