

Catalog Number: 185-1A1011-S030-1
Product ID: 7TCA296210R0012
EAN Number: 05016947001999
Status: Active

In-Line Waterproof Male Housing, 3 Pole Socket, 5-9mm Cable Range, Halogen Free, IP68, Plug & Socket Connector is Polycarbonate, Outer Housing is Glass Filled Nylon with Nitrile Rubber Seal, Black

North American Specifications (UNSPSC)

UNSPSC	39121421 Electrical connector assembly
IGCC	4586 Electrical connector assembly
Brand Name	Adaptaflex
Type	In-Line Waterproof Male Housing
Special Features	Halogen Free
Application	Light / Heavy Industrial
Conductor Range	5.0 to 9.0mm
Number Of Poles	3
Material	Polycarbonate Housing, Glass Filled Nylon with Nitrile Rubber Seal
Color	Black
Insulation	IP68
Temperature Rating	-25 Degrees C to +80 Degrees C

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	0.08 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com