



Actual

Catalog Number: B/144UNEF-M25/TC
Product ID: 7TCA296050R0097
EAN Number: 05020963002106
Status: Active

1-7/16 Inch UNEF Nickel Plated Brass Converter, Metric Thread Size M25

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Adaptaflex
Type	Converter
Special Features	Designed to Help Maintain System Integrity
Application	To Change Thread Type and Size for Two Piece of Conduit
Trade Size	1-7/16 Inch UNEF Thread to M25 Thread
Outside Diameter	41.0mm
Length	40 mm
Material	Nickel Plated Brass

European Specifications (ETIM)

ETIM	EC000938 Enlargement/reducing ring
Thread type inner thread	Metric
Thread size inner thread metric	25
Thread size outer thread (inch)	Other
Material	Brass
Nickel-plated	Y
Explosion-proof	N

Packaging

Inner Quantity	10
Outer Quantity	200
Outer Dimensions (inches)	14x14x6
Weight Uom	0.18 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com