



Representative

Catalog Number: AL28/075/C90/BLUS
Product ID: 7TCA296000R0767
EAN Number: 05020963052613
Status: Active
Replacement Catalog: AL28/075/C90/BLYI

90 Degree Conduit Fitting with No Locknut, Fixed External Male Thread, Nominal Conduit Size 28mm, 3/4 Inch NPT Thread, Polyamide (Nylon) 66, No Locknut, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with NPT Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 28mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	90 Degree
Cable Entry	3/4 Inch NPT Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	28mm
Degree of protection (IP)	IP66
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	NPT
Thread connection size	Other
Thread length	15mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Outer Quantity	400
Outer Dimensions (inches)	1x1x1
Weight Uom	0.06 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com