



Actual

Catalog Number: B/075UNEF-M20/TC
Product ID: 7TCA296050R0085
EAN Number: 05020963013942
Status: Active

3/4 Inch UNEF Nickel Plated Brass Converter, Metric Thread Size M20

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Adaptaflex
Type	Converter
Special Features	Designed to Help Maintain System Integrity
Application	To Change Thread Type and Size for Two Piece of Conduit
Trade Size	3/4 Inch UNEF Thread to M20 Thread
Outside Diameter	24.0mm
Length	23 mm
Material	Nickel Plated Brass

European Specifications (ETIM)

ETIM	EC000938 Enlargement/reducing ring
Thread type inner thread	Metric
Thread size inner thread metric	20
Thread size outer thread (inch)	3/4 inch
Material	Brass
Nickel-plated	Y
Explosion-proof	N

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.06 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com