



PRODUCT-DETAILS

PACH54/BL/100FT

54MM PA6 CONDUIT 100FT - BL



General Information

Extended Product Type:	PACH54/BL/100FT
Product ID:	7TCA296000R1910
EAN:	5020963019265
Catalog Description:	54MM PA6 CONDUIT 100FT - BL
Long Description:	Heavyweight Conduit, Nominal Conduit Size 54mm, NW Conduit Size 48, Coarse Conduit Pitch, Outside Diameter 54.5mm, Inside Diameter 46.0mm, Static Bend Radius 95mm, Reel Length 100 Feet, Polyamide (Nylon) 6, Black
Display Name:	PACH54/BL/100FT

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors - Rail, Heavy Industrial, Buildings & Machinery

Ordering

EAN:	5020963019265
-------------	---------------

UPC: 786210147000

Dimensions

Product Net Weight: 17.977365 lb
8.153 kg

Outside Diameter: 54.5 mm

Technical

Number of Batteries: 0

Color: Black

Material: Polyamide/Nylon 6

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963019265

Package Level 1 Height: 9.06 in
230 mm

Package Level 1 Depth / Length: 31.89 in
810 mm

Package Level 1 Width: 31.89 in
810 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001175 - Corrugated plastic hose

ETIM 9: EC001175 - Corrugated plastic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems > Adaptaflex Flexible Cable Protection

