
PRODUCT-DETAILS

B/M40/C

NPB M40 FEM-FEM COUPLER



General Information

Extended Product Type	B/M40/C
Product ID	7TCA296050R0149
EAN	5020963028458
Catalog Description	NPB M40 FEM-FEM COUPLER
Long Description	1-1/4 Inch Nickel Plated Brass Female Coupler, Metric Thread Size M40

Additional Information

Application	For Joining Two Male Threaded Items Together
Product Type	Female Coupler

Ordering

EAN	5020963028458
UPC	786210284408

Dimensions

Product Net Depth / Length	28 mm
----------------------------	-------

Technical

Number of Batteries	0
Material	Nickel Plated Brass

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	2 piece
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	B/M40/C
Instructions and Manuals	B/M40/C
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001172 - Coupler for corrugated plastic hoses
UNSPSC	39131707

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

