

PRODUCT-DETAILS

# B/M50/C

## NPB M50 FEM-FEM COUPLER



### General Information

Extended Product Type	B/M50/C
Product ID	7TCA296050R0151
EAN	5020963029080
Catalog Description	NPB M50 FEM-FEM COUPLER
Long Description	1-1/2 Inch Nickel Plated Brass Female Coupler, Metric Thread Size M50

### Additional Information

Application	For Joining Two Male Threaded Items Together
Product Type	Female Coupler

### Ordering

EAN	5020963029080
UPC	786210267951

### Dimensions

Product Net Depth / Length	37 mm
----------------------------	-------

---

## Technical

Number of Batteries	0
Material	Nickel Plated Brass

---

## Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	B/M50/C
Instructions and Manuals	B/M50/C
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---

## Classifications

ETIM 8	EC001172 - Coupler for corrugated plastic hoses
UNSPSC	39131707

---

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

