

PRODUCT-DETAILS

AT21/A/U/BLB

COUPLER - IP66.69/ NC21 COND BK/BLU



General Information

Extended Product Type	AT21/A/U/BLB
Product ID	7TCA296170R0224
EAN	5020963041570
Catalog Description	COUPLER - IP66.69/ NC21 COND BK/BLU
Long Description	Adaptalok ATS, Straight Body Swivel Coupler, Nominal Conduit Size 21mm, Polyamide (Nylon) 66/TPE, Black with Blue Elastomer

Additional Information

Application	For Coupling Two Corrugated Flexible Conduits
Product Type	Straight Body Swivel Coupler

Ordering

EAN	5020963041570
UPC	786210282183

Dimensions

Product Net Depth / Length	82 mm
----------------------------	-------

Technical

Number of Batteries	0
Color	Black/Blue
Material	Polyamide/Nylon 6.6 and TPE

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	10 piece
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AT21/A/U/BLB
Instructions and Manuals	AT21/A/U/BLB
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001172 - Coupler for corrugated plastic hoses
UNSPSC	39131707

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

