



PRODUCT-DETAILS

AT28/075/C90/BLY**90D PA66 FITTING 3/4NPT 28MM-BLY****General Information**

Extended Product Type:	AT28/075/C90/BLY
Product ID:	7TCA296170R0357
EAN:	5020963044823
Catalog Description:	90D PA66 FITTING 3/4NPT 28MM-BLY
Long Description:	Adaptalok ATS, 90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 28mm, 3/4 Inch NPT Thread, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer
Display Name:	AT28/075/C90/BLY

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN:	5020963044823
-------------	---------------

UPC: 786210283067

Dimensions

Product Net Weight: .09261 lb
42 g

Technical

Number of Batteries: 0
Color: Black/Yellow Elastomer
Material: Polyamide/Nylon 6.6
Size: NC 28mm

Environmental

WEEE Category: Product Not in WEEE Scope
RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 10 piece
Package Level 1 EAN: 5020963044823
Package Level 1 Height: 9.84 in
250 mm
Package Level 1 Depth / Length: 1 in
25 mm
Package Level 1 Width: 7.87 in
200 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618
RoHS Declaration: 9AKK107992A8994
REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001176 - Screw connection for corrugated plastic hose
ETIM 9: EC001176 - Screw connection for corrugated plastic hose
UNSPSC: 39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems > Adaptaflex Flexible Cable Protection

