



Representative

Catalog Number: AL13/PG9/C90/GR
Product ID: 7TCA296000R0262
EAN Number: 05020963012600
Status: Active

90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 13mm, PG9 Thread, Polyamide (Nylon) 66, Grey

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 13mm
Material	Polyamide/Nylon 6.6
Color	Gray
Connection	90 Degree
Cable Entry	PG09 Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	13mm
Degree of protection (IP)	IP66
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	PG9
Thread length	10mm
Material	Polyamide
Colour	Grey
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.02 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com