

Catalog Number: PRFSSS16/BL/50M
Product ID: 7TCA296100R0137
EAN Number: 05020963016004
Status: Active

Standard Weight Conduit, Nominal Conduit Size 16mm, NW Conduit Size 13, Fine Conduit Pitch, Outside Diameter 15.8mm, Inside Diameter 11.7mm, Static Bend Radius 45mm, Reel Length 50 Meters, Modified Polyamide (Nylon) 6 with Stainless Steel Overbraid, Black



Actual

- Very high UV resistance
- High flexibility
- Medium fatigue life
- High mechanical strength, high abrasion resistance
- Enhanced low fire hazard
- Halogen free
- Self-extinguishing
- Standard EMI screen rating

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	Standard Weight Conduit with Fine Pitch and Stainless Steel Overbraid
Special Features	Very High UV Protection
Application	Indoors, Public Areas, Rail Infrastructure
Trade Size	16mm
Outside Diameter	15.8mm
Inside Diameter	11.7mm
Length	50 m
Radius	45mm
Flexibility	High
Material	Modified Polyamide/Nylon 6 with Stainless Steel Overbraid
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Outer diameter	15.8mm
Inner diameter	11.7mm
Material	Polyamide 6
Operating temperature	-40-+120°C
Degree of protection (IP)	IP67
Fire resistance in accordance with UL94	V0
UV resistant	Y
Colour	Black
Sheathing material	Stainless steel braiding
Bending strength	Flexible
Lengthwise slotted	N
Approved according to LUL/British Standard	Y
	Y

Approved according to Lloyd's Register

TA

Approved according to NF F 16-101 Y

Packaging

Inner Quantity	1
Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	4.19 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com