








AT42/A/U/BLB

ats adaptalok straight swivel coupler 42mm Black/Blue



Technical

Colour	Black
Elastomer	Blue
Materials	Polyamide (Nylon) 66/TPE
Nominal Conduit Size	42mm
Temperature Range - Static	-50°C to +120°C
Temperature Range - Moving	-45°C to +120°C

Approvals	Blue Connector Green End Cap	IP Rating	Appropriate Conduit	Temperature Range
    	 	For use with: Type RA / RI / PR / PADDL / PF		Static Applications: -50°C to +120°C Moving Applications: -45°C to +120°C
		IP40	Yes	Fitting Characteristics 
		IP65	Yes	
		IP68	Yes (4 bar 30min)	
		IP69K	Yes	