



Actual

Catalog Number: AT42/A/U/BLY
Product ID: 7TCA296170R0609
EAN Number: 05020963040924
Status: Active

Adaptalok ATS, Straight Body Swivel Coupler, Nominal Conduit Size 42mm, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Adaptaflex
Type	Straight Body Swivel Coupler
Special Features	Very High UV Protection
Application	For Coupling Two Corrugated Flexible Conduits
Trade Size	NC 42mm
Outside Diameter	54.2mm
Length	110.4 mm
Installation Type	IP66 - IP69k
Material	Polyamide/Nylon 6.6 and TPE
Color	Black/Yellow Elastomer

European Specifications (ETIM)

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Operating temperature	-50-+120°C
Degree of protection (IP)	IP68
Model	Straight
Nominal size	42-42mm
Colour	Black

Packaging

Outer Quantity	2
Outer Dimensions (inches)	1x1x1
Weight Uom	0.17 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com