



Representative

Catalog Number: AT28/075/S45/GRB
Product ID: 7TCA296170R0366
EAN Number: 05020963046018
Status: Active

Adaptalok ATS, 45 Degree Conduit Fitting, Swivel External Male Thread, Nominal Conduit Size 28mm, 3/4 Inch NPT Thread, Polyamide (Nylon) 66, Nickel Plated Brass Thread/TPE, Grey with Blue Elastomer

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with NPT Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 28mm
Material	Polyamide/Nylon 6.6
Color	Gray/Blue Elastomer
Connection	45 Degree
Cable Entry	3/4 Inch NPT Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	28mm
Degree of protection (IP)	IP68
Model	45°-elbow
Revolving thread	Y
Construction type	External thread
Type of connection	Snap connection
Thread type	NPT
Thread connection size	Other
Thread length	13.5mm
Total height	82mm
Material	Polyamide
Material sealing	TPE
Colour	Grey
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.19 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com