



Representative

Catalog Number: AL16/050/C90/BL YI
Product ID: 7TCA296000R0320
EAN Number: 05020963014444
Status: Active

90 Degree Conduit Fitting with Locknut and Sealing Washer, Fixed External Male Thread, Nominical Conduit Size 16mm, 1/2 Inch NPT Thread, With Locknut and Sealing Washer, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with NPT Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 16mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	90 Degree
Cable Entry	1/2 Inch NPT Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	16mm
Degree of protection (IP)	IP66
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	NPT
Thread connection size	Other
Thread length	13mm
Material	Polyamide
Material sealing	TPE
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Outer Quantity	100
Outer Dimensions (inches)	8x8x8
Weight Uom	0.03 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com