



Representative

Catalog Number: ASC42/M40/A/BL
Product ID: 7TCA296000R1545
EAN Number: 05020963014024
Status: Active

Adaptaseal Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 42mm, M40 Thread, Polyamide (Nylon) 66, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 42mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	Straight
Cable Entry	M40 Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	42mm
Degree of protection (IP)	IP68
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread type	Metric
Thread connection size	M40 x 1.5
Thread length	16mm
Total length	58mm
Total height	58.5mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	1.4x1.5x1.5
Outer Quantity	50
Outer Dimensions (inches)	1.4x1.5x1.5
Weight Uom	0.12 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com