



Representative

**Catalog Number:** AL28/M25/CS90/GR  
**Product ID:** 7TCA296000R0816  
**EAN Number:** 05020963033797  
**Status:** Active

90 Degree Conduit Fitting, Swivel External Male Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66, Nickel Plated Brass Thread, Grey

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 28mm
Material	Polyamide/Nylon 6.6
Color	Gray
Connection	90 Degree
Cable Entry	M25 Thread

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	28mm
Degree of protection (IP)	IP66
Model	90°-elbow
Revolving thread	Y
Construction type	External thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M25 x 1.5
Thread length	12.2mm
Material	Polyamide
Colour	Grey
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	N

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.15 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com