



Premium Battery Cable Assemblies

UL1426 Tinned Boat Cable

- Premium, fine stranded UL1426 tinned copper battery cable for maximum conductivity and flexibility
- Flame retardant, UV inhibited cable rated at 600V and 105°C
- Tinned copper lugs to avoid corrosion and extend life
- 3:1 heatshrink tubing over the electrical connection to seal out moisture and provide strain relief

Color	Length	Stud Size	Part #
4 AWG (21 mm²)			
Black	18"	45.7 cm	5/16" 7.93 mm 189130
	32"	81.2 cm	5/16" 7.93 mm 189134
	48"	121.9 cm	5/16" 7.93 mm 189136
Red	18"	45.7 cm	3/8" 9.5 mm 189131
	32"	81.2 cm	3/8" 9.5 mm 189135
	48"	121.9 cm	3/8" 9.5 mm 189137

Color	Length	Stud Size	Part #
2 AWG (34 mm²)			
Black	18"	45.7 cm	5/16" 7.93 mm 189140
	32"	81.2 cm	5/16" 7.93 mm 189144
	48"	121.9 cm	5/16" 7.93 mm 189146
Red	18"	45.7 cm	3/8" 9.5 mm 189141
	32"	81.2 cm	3/8" 9.5 mm 189145
	48"	121.9 cm	3/8" 9.5 mm 189147

For continuous current draws up to:	Use battery cable assemblies
136 amps	4 AWG
178 amps	2 AWG

Safety Duplex Cable

UL 1426 Tinned Boat Cable

Conductor colors: red and yellow

Flat Cable



Spool Length	Part #	Nominal O.D.	Wt. per 1000'
18/2 AWG (2x0.8 mm²)			
100'	124910		
250'	124925	3/16"x9/32"	49 lbs
500'	124950	5x7 mm	22.2 kg
1000'	124999		
16/2 AWG (2x1 mm²)			
100'	124710		
250'	124725	3/16"x5/16"	51 lbs
500'	124750	5x8 mm	23.1 kg
1000'	124799		
14/2 AWG (2x2 mm²)			
25'	124502		
100'	124510		
250'	124525	7/32"x11/32"	65 lbs
500'	124550	6x9 mm	29.5 kg
1000'	124599		

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
12/2 AWG (2x3 mm²)			
100'	124310		
250'	124325	7/32"x3/8"	82 lbs
500'	124350	6x10 mm	37.3 kg
10/2 AWG (2x5 mm²)			
25'	124102		
100'	124110		
250'	124125	1/4"x15/32"	128 lbs
400'	124140	6x12 mm	58.2 kg
800'	124180		
8/2 AWG (2x8 mm²)			
50'	123905	11/32"x5/8"	230 lbs
100'	123910	9x16 mm	104.5 kg
6/2 AWG (2x13 mm²)			
50'	123705	13/32"x3/4"	364 lbs
100'	123710	10x19 mm	165.5 kg

Round Cable



Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/2 AWG (2x1 mm²)			
100'	126710		
250'	126725	5/16"	49 lbs
500'	126750	8 mm	22.2 kg
14/2 AWG (2x2 mm²)			
100'	126510		
250'	126525	11/32"	63 lbs
500'	126550	9 mm	28.6 kg

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
12/2 AWG (2x3 mm²)			
100'	126310		
250'	126325	13/32"	80 lbs
500'	126350	10 mm	36.3 kg