

Duplex Cable

Conductor colors: black and red

Flat Cable



| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|--------------|---------------|
| 18/2 AWG (2x0.8 mm ²) | | | |
| 100' | 121910 | | |
| 250' | 121925 | 3/16"x9/32" | 49 lbs |
| 500' | 121950 | 5x7 mm | 22.2 kg |
| 16/2 AWG (2x1 mm ²) | | | |
| 100' | 121710 | | |
| 250' | 121725 | 3/16"x5/16" | 51 lbs |
| 500' | 121750 | 5x8 mm | 23.1 kg |
| 1000' | 121799 | | |
| 14/2 AWG (2x2 mm ²) | | | |
| 100' | 121510 | | |
| 250' | 121525 | 7/32"x11/32" | 65 lbs |
| 500' | 121550 | 6x9 mm | 29.5 kg |
| 1000' | 121599 | | |

| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|--------------|---------------|
| 12/2 AWG (2x3 mm ²) | | | |
| 100' | 121310 | | |
| 250' | 121325 | 7/32"x3/8" | 82 lbs |
| 500' | 121350 | 6x10 mm | 37.3 kg |
| 10/2 AWG (2x5 mm ²) | | | |
| 100' | 121110 | | |
| 250' | 121125 | 1/4"x15/32" | 128 lbs |
| 400' | 121140 | 6x12 mm | 58.2 kg |
| 800' | 121180 | | |
| 8/2 AWG (2x8 mm ²) | | | |
| 50' | 120905 | | |
| 100' | 120910 | 11/32"x5/8" | 230 lbs |
| 250' | 120925 | 9x16 mm | 104.5 kg |
| 6/2 AWG (2x13 mm ²) | | | |
| 50' | 120705 | 13/32"x3/4" | 364 lbs |
| 100' | 120710 | 10x19 mm | 165.5 kg |

Triplex Cable

Conductor colors: black, green and white

Flat Cable



| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|--------------|---------------|
| 16/3 AWG (3x1 mm ²) | | | |
| 100' | 131710 | | |
| 250' | 131725 | 3/16"x15/32" | 75 lbs |
| 500' | 131750 | 5x12 mm | 34 kg |
| 1000' | 131799 | | |
| 14/3 AWG (3x2 mm ²) | | | |
| 100' | 131510 | | |
| 250' | 131525 | 7/32"x1/2" | 96 lbs |
| 500' | 131550 | 6x13 mm | 43.6 kg |
| 900' | 131590 | | |
| 12/3 AWG (3x3 mm ²) | | | |
| 25' | 131302 | | |
| 100' | 131310 | 7/32"x17/32" | 125 lbs |
| 250' | 131325 | 6x14 mm | 56.8 kg |
| 700' | 131370 | | |

| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|---------------|---------------|
| 10/3 AWG (3x5 mm ²) | | | |
| 100' | 131110 | | |
| 300' | 131130 | 1/4"x21/32" | 186 lbs |
| 500' | 131150 | 6x17 mm | 84.5 kg |
| 8/3 AWG (3x8 mm ²) | | | |
| 25' | 130902 | | |
| 50' | 130905 | 3/8"x1" | 287 lbs |
| 100' | 130910 | 10x25 mm | 130.4 kg |
| 6/3 AWG (3x13 mm ²) | | | |
| 50' | 130705 | 7/16"x1-3/16" | 470 lbs |
| 100' | 130710 | 11x30 mm | 213.6 kg |

Round Cable



| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|--------------|---------------|
| 16/3 AWG (3x1 mm ²) | | | |
| 100' | 133710 | 11/32" | 75 lbs |
| 250' | 133725 | 9 mm | 34 kg |
| 14/3 AWG (3x2 mm ²) | | | |
| 100' | 133510 | | |
| 250' | 133525 | 13/32" | 96 lbs |
| 900' | 133590 | 10 mm | 43.6 kg |

| Spool Length | Part # | Nominal O.D. | Wt. per 1000' |
|--|---------------|--------------|---------------|
| 12/3 AWG (3x3 mm ²) | | | |
| 100' | 133310 | 7/16" | 125 lbs |
| 250' | 133325 | 11 mm | 56.8 kg |

Related Products



Cutting & Stripping Tools
pages 50-51



Wire Seals
page 41