



European Color Code AC Cable
Premium Tinned Copper, Class K Stranding
 Conductor colors: blue, brown and green with yellow stripe

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
10/3 AWG (3x5 mm²)			
500'	131151	1/4"x21/32" 6x17 mm	186 lbs 84.5 kg



Flat Trailer Cable
Tinned Boat Cable
 Conductor colors: yellow, white, green and brown

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/4 AWG (4x1 mm²)			
100'	154010	3/16"x9/16"	105 lbs
300'	154030	4x14 mm	47.7 kg



Signal Cable
Tinned Boat Cable
 Conductor colors: red and black

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
20/2 AWG (2x0.5 mm²)			
25'	189303		
100'	122010	5/32"x1/4"	18 lbs
500'	122050	4x6.4 mm	8.1 kg



Round Signal
100% Mylar Foil Shield and Drain Tinned Boat Cable
 Conductor colors: black, red, green, blue, brown, orange, purple and yellow


Spool Length	Part #	Nominal O.D.	Wt. per 1000'
20/8 AWG (8x0.5 mm²)			
100'	158010	5/16"	63 lbs
250'	158025	7.9 mm	28.6 kg



Twisted Pairs w/ Shield
Premium Tinned Copper
 Color conductors: red and black

- For all metal boats and around sensitive electronics
- Ultra flexible stranding is tinned for corrosion resistance
- 93% Tinned copper shield for maximum EMI and RFI rejection
- 2-3" lay for interference cancellation

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
14/2 AWG (2x2 mm²)			
100'	141410	.330"	73.2 lbs
250'	141425	8.4 mm	33.3 kg



Round Instrument Cable
100% Mylar Foil Shield & Drain Wire
UL 1426 Tinned Boat Cable
 Color conductors: red, black and bare

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
20/3 AWG (3x0.5 mm²)			
100'	153010	7/32"	30 lbs
500'	153050	5.6 mm	13.6 kg



Flat Ribbon Bonded Cable
Premium Tinned Bonded Copper
 Conductor colors: red and black

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/2 AWG (2x1 mm²)			
100'	153110	1/8"x1/4"	32 lbs
500'	153150	3.2x6.4 mm	14.5 kg



Flat Ribbon Bonded Trailer Cable
Premium Tinned Bonded Copper
 Conductor colors: brown, green, white and yellow

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/4 AWG (4x1 mm²)			
100'	154510	1/8"x1/2"	29.2 lbs
250'	154525	3.2x12.7 mm	13.2 kg