



GTO 15 High Voltage Cable (15000V)

- Color conductors: white
- Coupler output to antenna

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
14 AWG (2 mm²)			
25'	150102	1/4"	38 lbs
100'	150110	6.4 mm	17.2 kg



Round Mast UL 1426 Tinned Boat Cable

- Color conductors: black, blue, green, brown and red

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
14/5 AWG (5x2 mm²)			
100'	155010	1/2"	160 lbs
500'	155050	12.7 mm	79.5 kg



Super Flex Audio Cable Premium Tinned Copper

- Super flexible, easy to run
- Clear jacket to blend into the environment
- Drawn copper, unidirectional lay for ultimate in sound quality
- Tinned copper for corrosion resistance in the marine environment

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
18/2 AWG (2x0.8 mm²)			
100'	142810	.265" 6.7 mm	29 lbs 13 kg
16/2 AWG (2x1 mm²)			
100'	142610	.319" 8.1 mm	51 lbs
250'	142625		23.1 kg
500'	142650		
14/2 AWG (2x2 mm²)			
100'	142410	.345" 8.8 mm	65 lbs
250'	142425		29.5 kg
1000'	142499		



Bilge Pump Cable Premium Tinned Copper

- Color conductors: black, brown and red
Insulation: grey
- Conductors specifically for bilge pumps
 - Oil resistant
 - STOW - A - Water resistant jacket

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/3 AWG (3x1 mm²)			
100'	156610	.348"	78 lbs
250'	156625	8.85 mm	35.5 kg
14/3 AWG (3x2 mm²)			
100'	156410	.377" 9.6 mm	99 lbs
250'	156425		45.0 kg
500'	156450		



Shore Power Cord

- Conductor colors: black, white, green (and red 100319 only)
- High visibility yellow jacket is oil and sunlight resistant
 - Ultra flexible insulation is abrasion resistant for "hard service" applications
 - 600 volt rated for extra heavy-duty service
 - 16/3 is 300 volt cable
 - Temp rating: 140°F (60°C)

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
16/3 Phone			
300'	153530	5/16" 6 mm	75 lbs 34 kg
10/3 STOW			
250'	153725	21/32" 17 mm	284 lbs 129 kg
10/3 STW			
250'	SPC103	21/32" 17 mm	284 lbs 129 kg

Spool Length	Part #	Nominal O.D.	Wt. per 1000'
6/3 STOW			
250'	153925	7/8"	540 lbs
per/ft**	100320	22 mm	254.4 kg
6/4 STW			
per/ft**	100319	29/32" 23 mm	695 lbs 316 kg

*SPC103, 100320 and 100319 are not tinned wire
**50 ft minimum