

## Anchor Marine Grade™ Wire & Cable

- Anchor Marine Grade™ wire and cable is manufactured from tinned copper stranding for maximum protection against corrosion and electrolysis. Ultra flexible (Type 3) stranding resists fatigue due to vibration and flexing.
- Anchor's proprietary premium vinyl insulation stays flexible even in extreme cold (-40°C) and resists salt water, battery acid, oil, gasoline and ultra-violet radiation. Exclusive insulation is rated at 600 volts, 105°C dry and 75°C wet, and is resistant to heat and abrasion.
- Exceeds all UL 1426, US Coast Guard Charter boat (CFR Title 46) and ABYC standards.
- See pages 72–76 for ABYC wiring guidelines and technical data.



### Primary Wire 18–14 AWG

#### 18 AWG (0.8 mm<sup>2</sup>)

Color	Ft	Part #
Black	35	180003
	100	100010
	250	100025
	500	100050
	1000	100099
Dk Blue	35	180103
	100	100110
	250	100125
	500	100150
	1000	100199
Brown	35	180203
	100	100210
	250	100225
	500	100250A
	1000	100299
Green	35	180303
	100	100310
	250	100325
	500	100350
	1000	100399
Grey	35	180403
	100	100410
	250	100425
	500	100450
	1000	100499
Orange	35	180503
	100	100510
	250	100525
	500	100550
	1000	100599
Pink	35	180603
	100	100610
	250	100625
	500	100650
	1000	100699
Purple	35	180703
	100	100710
	250	100725
	500	100750
	1000	100799
Red	35	180803
	100	100810
	250	100825
	500	100850
	1000	100899

#### 18 AWG (0.8 mm<sup>2</sup>)

Color	Ft	Part #
White	35	180903
	100	100910
	250	100925
	500	100950
	1000	100999
Yellow	35	181003
	100	101010
	250	101025
	500	101050
	1000	101099

#### 16 AWG (1 mm<sup>2</sup>)

Color	Ft	Part #
Lt Blue	100	101910
	250	101925
	500	101950
	1000	101999
	1000	102099
Black	25	182003
	100	102010
	250	102025
	500	102050
	1000	102099
Dk Blue	25	182103
	100	102110
	250	102125
	500	102150
	1000	102199
Brown	25	182203
	100	102210
	250	102225
	500	102250
	1000	102299
Green	25	182303
	100	102310
	250	102325AA
	500	102350
	1000	102399
Grey	25	182403
	100	102410
	250	102425
	500	102450
	1000	102499

#### 16 AWG (1 mm<sup>2</sup>)

Color	Ft	Part #
Orange	25	182503
	100	102510
	250	102525
	500	102550
	1000	102599
Pink	25	182603
	100	102610
	250	102625
	500	102650
	1000	102699
Purple	25	182703
	100	102710
	250	102725
	500	102750
	1000	102799
Red	25	182803
	100	102810
	250	102825
	500	102850
	1000	102899
White	25	182903
	100	102910
	250	102925
	500	102950
	1000	102999
Yellow	25	183003
	100	103010
	250	103025
	500	103050
	1000	103099

#### 14 AWG (2 mm<sup>2</sup>)

Color	Ft	Part #
Lt Blue	100	103910
	250	103925
	500	103950
	1000	103999
	1000	104099
Black	18	184003
	100	104010
	250	104025
	500	104050
	1000	104099
Dk Blue	18	184103
	100	104110
	250	104125
	500	104150
	1000	104199

#### 14 AWG (2 mm<sup>2</sup>)

Color	Ft	Part #
Brown	18	184203
	100	104210
	250	104225
	500	104250
	1000	104299
Green	18	184303
	100	104310
	250	104325
	500	104350
	1000	104399
Grey	18	184403
	100	104410
	250	104425
	500	104450
	1000	104499
Orange	18	184503
	100	104510
	250	104525
	500	104550
	1000	104599
Pink	18	184603
	100	104610
	250	104625
	500	104650
	1000	104699
Purple	18	184703
	100	104710
	250	104725
	500	104750
	1000	104799
Red	18	184803
	100	104810
	250	104825
	500	104850
	1000	104899
White	18	184903
	100	104910
	250	104925
	500	104950
	1000	104999
Yellow	18	185003
	100	105010
	250	105025
	500	105050
	1000	105099