

# ACSEW Control Operators: Mushroom Head Push Button Components

## Momentary Contact. Explosionproof

**NEC/CEC:**  
 Class I, Division 1 and 2, Groups B, C, D  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 4, 7BCD, 9EFG

**NEC/CEC — cULus Optional:**  
 Class I, Division 1 and 2, Groups B, C, D  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 4, 7BCD, 9EFG

### Catalog Numbering Guide

**AE**  
 NEC/CEC Certified  
 Appleton Explosionproof

**P**  
 Push Button

**M**  
 Mushroom Head, Momentary

**B**  
 Color:  
 B - Black  
 R - Red  
 G - Green

**A**  
 Contact Arrangement:  
 A - 1 NO  
 B - 2 NO  
 C - 1 NC  
 D - 2 NC  
 E - 1 NO and 1 NC  
 F - 2 NO and 2 NC

**L**  
 Long Barrel:  
 Omit for Short Barrel



Contacts ①	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
1 NO	Black	AEPMBA	AEPMBA-L
1 NO	Red	AEPMRA	AEPMRA-L
1 NO	Green	AEPMGA	AEPMGA-L
2 NO	Black	AEPMBB	AEPMBB-L
2 NO	Red	AEPMRB	AEPMRB-L
2 NO	Green	AEPMGB	AEPMGB-L
1 NC	Black	AEPMBC	AEPMBC-L
1 NC	Red	AEPMRC	AEPMRC-L
1 NC	Green	AEPMGC	AEPMGC-L

Contacts ①	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
2 NC	Black	AEPMBD	AEPMBD-L
2 NC	Red	AEPMRD	AEPMRD-L
2 NC	Green	AEPMGD	AEPMGD-L
1 NO and 1 NC	Black	AEPMBE	AEPMBE-L
1 NO and 1 NC	Red	AEPMRE	AEPMRE-L
1 NO and 1 NC	Green	AEPMGE	AEPMGE-L
2 NO and 2 NC	Black	AEPMBF	AEPMBF-L
2 NO and 2 NC	Red	AEPMRF	AEPMRF-L
2 NO and 2 NC	Green	AEPMGF	AEPMGF-L

① NO = Normally Open; NC = Normally Closed.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875").  
 For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.

CONTROLS: NEC/CEC EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES

APPLETON™