

ACSEW Control Operators: Mushroom Head Push Button Components

Maintained Contact. Explosionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC — cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

Catalog Numbering Guide

AE
 NEC/CEC Certified
 Appleton Explosionproof

P
 Push Button

MC
 Mushroom Head, Maintained

B
 Color:
 B - Black
 R - Red
 G - Green

A
 Contact Arrangement:
 A - 1 NO
 B - 2 NO
 C - 1 NC
 D - 2 NC
 E - 1 NO and 1 NC
 F - 2 NO and 2 NC

L
 Long Barrel:
 Omit for Short Barrel



Contacts ①	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
1 NO	Black	AEPMCBA	AEPMCBA-L
1 NO	Red	AEPMCRA	AEPMCRA-L
1 NO	Green	AEPMCGA	AEPMCGA-L
2 NO	Black	AEPMCB B	AEPMCB B-L
2 NO	Red	AEPMCR B	AEPMCR B-L
2 NO	Green	AEPMCG B	AEPMCG B-L
1 NC	Black	AEPMCBC	AEPMCBC-L
1 NC	Red	AEPMCRC	AEPMCRC-L
1 NC	Green	AEPMCGC	AEPMCGC-L

Contacts ①	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
2 NC	Black	AEPMCBD	AEPMCBD-L
2 NC	Red	AEPMCRD	AEPMCRD-L
2 NC	Green	AEPMCGD	AEPMCGD-L
1 NO and 1 NC	Black	AEPMCBE	AEPMCBE-L
1 NO and 1 NC	Red	AEPMCRE	AEPMCRE-L
1 NO and 1 NC	Green	AEPMCGE	AEPMCGE-L
2 NO and 2 NC	Black	AEPMCBF	AEPMCBF-L
2 NO and 2 NC	Red	AEPMCRF	AEPMCRF-L
2 NO and 2 NC	Green	AEPMCGF	AEPMCGF-L

① NO = Normally Open; NC = Normally Closed.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875"). For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.

CONTROL: NEC/CEC EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES

APPLETON