

# Armored Cable and Flexible Metal Conduit Connectors

**NEC/CEC:**  
Rated for Ordinary Locations

**NEC/CEC:**  
Listed for Ordinary Locations

## Combination Coupling 3/8" Flexible Metal Conduit to 1/2" EMT

### Applications

- To couple 3/8" flexible metal conduit to 1/2" EMT conduit.

### Features

- Furnished with locknut.

### Standard Material

- Zinc diecast

## Armored Ground Wire and Nonmetallic Sheathed Cable <sup>①</sup> Connector

### Applications

- To ground and secure armored ground wire and nonmetallic sheathed cable to boxes and enclosures.

### Features

- Furnished with locknut.
- Male hub threads — NPS.


### Standard Material

- Malleable iron/zinc plated


### NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-11852, E-11853
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 009795, 065178
- NEMA: FB-1


**Illustrated Dimensions**



**Illustrated Dimensions**



7287V



7230V

Flexible Conduit Size (Inches)	Cable Opening in Millimeters (Inches)		Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number
	Max.	Min.	A	B	C		
3/8	16.0 (0.63)	5.6 (0.22)	22.4 (0.88)	10.4 (0.41)	31.8 (1.25)	3.40 (7.50)	TW38-50DC <sup>②</sup>

Flexible Conduit Size (Inches)	Cable Opening in Millimeters (Inches)		Bushed Hole Diameter	Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number
	Max.	Min.		A	B	C		
1/2	23.9 (0.94)	10.4 (0.41)	14.9 (0.59)	27.7 (1.09)	10.4 (0.41)	47.8 (1.88)	7.71 (17.00)	7287V
1/2 (3/4" knockout)	23.9 (0.94)	14.9 (0.59)	19.8 (0.78)	27.7 (1.09)	11.2 (0.44)	47.8 (1.88)	8.62 (19.00)	7288V
3/8 (1/2" knockout)	16.0 (0.63)	8.6 (0.34)	-	16.0 (0.63)	11.2 (0.44)	25.4 (1.00)	3.18 (7.00)	7230V

<sup>①</sup> Select connectors by physical dimensions of cable as dimensions may vary between manufacturers.

<sup>②</sup> UL Listed and CSA Certification not applicable.