

ETP™ 6000US Steel EMT Compression Couplings

NEC/CEC:
Listed for Ordinary Locations

Application

- To ground and secure EMT raceway sections together.

Features

- Made in the U.S.A.
- Concretetight.
- Raintight (wet locations) Canada.

Material/Finish

- Body and nut: steel.
- Steel/zinc plated

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: (1/2 - 3) E14815
- CSA Standard: C22.2 No. 18.3
- cUL Listed: (1/2 - 3) E14815
- NEMA: FB-1



6050S — 6200US



6250US — 6400US

Trade Size (Inches)	Dimensions in Millimeters (Inches)		Catalog Number
	Body Length	Maximum Diameter	
1/2	34.0 (1.34)	0.97 (24.6)	6050US
3/4	34.0 (1.34)	31.0 (1.22)	6075US
1	35.8 (1.41)	38.1 (1.50)	6100US
1-1/4	44.5 (1.75)	48.5 (1.91)	6125US
1-1/2	47.8 (1.88)	54.9 (2.16)	6150US
2	54.1 (2.13)	68.3 (2.69)	6200US
2 - 1/2	139.7 (5.50)	104.9 (4.13)	6250US
3	139.7 (5.50)	119.1 (4.69)	6300US
3 - 1/2	143.0 (5.63)	135.6 (5.34)	6350US
4	146.1 (5.75)	149.4 (5.88)	6400US