

NEER™ Zinc Bushed Conduit Nipples

NEC/CEC:
Listed for Ordinary Locations

Applications

- Use through knockout to connect box to conduit coupling.
- Use with a locknut to connect two boxes side by side or back to back.
- Use with a locknut to connect fixture housings to continuous runs.

Features

- Male hub threads — NPS.
- Available with insulated throat.

Material/Finish

- Zinc diecast

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14814
- CSA Standard: C22.2 No. 18
- CSA Certified: 065178
- NEMA: FB-1



CNI-100

| Trade Size (Inches) | Dimensions in Millimeters (Inches) | | |
|------------------------|------------------------------------|----------------|-------------------|
| | Maximum Diameter | Body Length | Catalog Number |
| 1/2 | 23.9 (0.94) | 15.0 (0.59) | CNN-100 |
| 3/4 | 30.2 (1.19) | 18.3 (0.72) | CNN-200 |
| 1 | 35.1 (1.38) | 21.6 (0.85) | CNN-300 |
| 1-1/4 | 44.2 (1.74) | 22.1 (0.87) | CNN-400 |
| 1-1/2 | 53.8 (2.12) | 22.9 (0.90) | CNN-500 |
| 2 | 64.8 (2.55) | 29.2 (1.15) | CNN-600 |
| 2-1/2 | 81.5 (3.21) | 36.3 (1.43) | CNN-700 |
| 3 | 96.5 (3.80) | 36.3 (1.43) | CNN-800 |
| 3-1/2 | 108.5 (4.27) | 36.3 (1.43) | CNN-900 |
| 4 | 121.7 (4.79) | 36.3 (1.43) | CNN-1000 |

| Trade Size (Inches) | Dimensions in Millimeters (Inches) | | |
|------------------------|------------------------------------|----------------|-------------------|
| | Maximum Diameter | Body Length | Catalog Number |
| 1/2 | 23.9 (0.94) | 17.0 (0.67) | CNI-100 |
| 3/4 | 30.2 (1.19) | 20.3 (0.80) | CNI-200 |
| 1 | 35.1 (1.38) | 23.6 (0.93) | CNI-300 |
| 1-1/4 | 44.2 (1.74) | 24.1 (0.95) | CNI-400 |
| 1-1/2 | 53.8 (2.12) | 24.9 (0.98) | CNI-500 |
| 2 | 64.8 (2.55) | 31.2 (1.23) | CNI-600 |