

GHPH Power Hook for Industrial High Bay Luminaire

Receptacle and Hook and Loop

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC:

Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.

Features

- Permit quick disconnect and removal of fixture for maintenance.
- Available in pendant or feed-thru.
- Available with matching cord set.

Standard Materials

- Malleable iron with steel cover
- Screws: stainless steel

Standard Finishes

- Malleable iron parts: triple-coat—(1) zinc electroplate, (2) chromate, and (3) epoxy powder coat
- Steel parts: zinc electroplate

NEC/CEC Certifications and Compliances

- UL Standard: UL 57
- CSA Standard: C22.2 No. 9, C22.2 No. 250
- CSA Certified: 009349

GHPHP and GHPHT — Receptacle Hangers



GHPHP



GHPHT

| | | Conduit Hub Size (Inches) | Voltage | Hubbell Plug | Catalog Number | |
|---|-------|---------------------------|----------|--------------|----------------|-----------|
| | | | | | Pendant | Feed-Thru |
| Furnished with assembled FS box, EFHM, safety lock, receptacle, and steel cover. Supports 90.7kg (200 lbs). | | | | | | |
| <p>215.9 (8.5) for GHPHP 153.9 (6.06) for GHPHT</p> | GHPHP | 3/4 | 120 | L5-15P | GHPHP12 | GHPHT12 |
| | GHPHT | 3/4 | 208, 240 | L6-15P | GHPHP24 | GHPHT24 |
| | | 3/4 | 277 | L7-15P | GHPHP27 | GHPHT27 |
| | | 3/4 | 347 | L37-20P | GHPHP34 ① | GHPHT34 ① |
| | | 3/4 | 480 | L8-20P | GHPHP48 | GHPHT48 |
| | | 3/4 | 600 | L9-20P | GHPHP60 ① | GHPHT60 ① |

Cord Sets — With Loop — Supplied with 600 V, 90°C 3 conductor No. 16 SOW cable, locking plug and 3/4" FHLM loop

| | | Voltage | Amperes | 0.6 m (2' ft) Cord | 0.9 m (3 ft) Cord | 1.21 m (4 ft) Cord |
|--|--|----------|---------|--------------------|-------------------|--------------------|
| | | 120 | 15 | G-HCPL-2-12 | G-HCPL-3-12 | G-HCPL-4-12 |
| | | 208, 240 | 15 | G-HCPL-2-24 | G-HCPL-3-24 | G-HCPL-4-24 |
| | | 277 | 15 | G-HCPL-2-27 | G-HCPL-3-27 | G-HCPL-4-27 |
| | | 347 | 20 | G-HCPL-2-34 ① | G-HCPL-3-34 ① | G-HCPL-4-34 ① |
| | | 480 | 20 | G-HCPL-2-48 | G-HCPL-3-48 | G-HCPL-4-48 |
| | | 600 | 20 | G-HCPL-2-60 ① | G-HCPL-3-60 ① | G-HCPL-4-60 ① |

Fuse and Cartridge — Cartridges are furnished complete with two 254 mm (10") long high temperature wire leads and 600 Volt fuse

| | | Amperes | Catalog Number |
|--|--|---------|----------------|
| | | 6 | G-F6 |
| | | 10 | G-F10 |
| | | 20 | G-F20 |
| | | 30 | G-F30 |

① Certified to meet the Canadian Electrical Code (CEC) only.

POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS

