

Unicode™ 2 Series Key Release Mushroom Push Buttons

Components for Increased Safety Enclosures

NEC/CEC:
 Class I, Division 2 Groups A, B, C, D
 Class I, Zone 1, Ex e d IIC Gb
 Class I, Zone 1, AEx e d IIC Gb
 Class II, Division 1, Groups E, F, G

NEC/CEC:
 Class II, Zone 21, Ex tb IIIC Db
 Class II, Zone 21, AEx t IIIC Db
 Class III, Division 1
 IP6X

ATEX/IECEX:
 Zone 1 and 2 – 21 and 22
 Ⓜ II 2 GD
 IP66 - IK10

CONTROLS: NEC/CEC, ATEX/IECEX INCREASED SAFETY CONTROL STATIONS

Features

- Can be equipped with up to three Unicode 2 Series Contact Blocks (UCB) contact blocks.
- Globally certified.
- Available in TS35 rail mounted or panel mounted.

Standard Materials

- Body: thermosetting plastic
- Seal: ethylene propylene diene Monomer (M-class) rubber (EPDM)

NEC/CEC Certifications and Compliances

- Certification Type AUX
 - Rated Ambient Temperature: -55 °C to +70 °C (-67 °F to +158 °F)
- UL Standards: UL No. 61010-1 (2nd Edition), UL 60079-0 (5th Edition 2009), UL 60079-1 (6th Edition 2009), UL 60079-7 (Ed 4th 2008), UL 60079-31:2009
- UL Certificate: E184198
- CAN/CSA Standards: C22.2 No. 0-10, C22.2 No. 61010-1-04, C22.2 No 213 (2nd Edition), C22.2 No. 60079-0:07, C22.2 No. 60079-1:07, No. 60079-7:03, No. 60079-31:12, E61241-1-1:02, C22.2 No. 60529:05 (R 2010)
- CSA Certificate: 2661552
- Other Standards: ANSI/ISA-12.12.01 (2013), ANSI/ISA-61241-0 (12.10.02)-2006 (R2011), ANSI/ISA-61241-1 (12.10.03)-2006 (R2011), ANSI/IEC 60529-2004

ATEX Certifications and Compliances

- Certification Type AUX
 - Gas: Zone 1 and 2
 - Conforming to ATEX 94/9/CE: Ⓜ II 2 G
 - Type of Protection: Ex e II
 - Dust: Zone 21 and 22
 - Conforming to ATEX 94/9/CE: Ⓜ II 2 D
 - Type of Protection: Ex tD A21
- Surface Temperature: -20 °C to +70 °C (-4 °F to +158 °F)
- CE Declaration of Conformity: 5C206
- ATEX Certificate: LCIE 00 ATEX 0002U
- Index of Protection according EN/IEC 60529: IP66
- Impact Resistance (shock): 7 Joules

EURASEC Certification

- EURASEC RU C-FR. Г605.В00909

Other Certification ①

- INMETRO Certificate: BVC 11.0644-U



UCOR
(rail mounted contacts)




UCOP
(panel mounted contacts)




UCB
Contact Block

Dimensions in Millimeters (Inches)

Rail Mounted Contacts



Panel Mounted Contacts



① INMETRO certification available on special request only. Contact your local sales representative for more information.

Unicode™ 2 Series Key Release Mushroom Push Buttons

Components for Increased Safety Enclosures

NEC/CEC:

Class I, Division 2 Groups A, B, C, D
 Class I, Zone 1, Ex e d IIC Gb
 Class I, Zone 1, AEx e d IIC Gb
 Class II, Division 1, Groups E, F, G

NEC/CEC:

Class II, Zone 21, Ex tb IIIC Db
 Class II, Zone 21, AEx t IIIC Db
 Class III, Division 1
 IP6X

ATEX/IECEX:

Zone 1 and 2 – 21 and 22
 II 2 GD
 IP66 - IK10

CONTROLS: NEC/CEC, ATEX/IECEX INCREASED SAFETY CONTROL STATIONS

	Weight kg (lb)		Volume dm ³ (in ³)		Pack	Catalog Number	
	Rail Mounted	Panel Mounted	Rail Mounted	Panel Mounted		Rail Mounted	Panel Mounted
Key Release Mushroom Head Push Button (contact block to be ordered separately)							
<i>For legend plates, guards and blanking plugs see accessories page.</i>							
Red	0.085 (0.183)	0.096 (0.212)	0.09 (5.49)	0.25 (15.26)	1	UC0R	UC0P
1-Pole Contact Blocks							
1 x NO						UCB5R	UCB5P
1 x NC	0.032 (0.071)		0.06 (3.66)		1	UCB9R	UCB9P
Spare Parts							
Spare key (type 4A 185)	—		—			SK4A185	SK4A185
Rail to panel mounted conversion adaptor	0.02 (0.04)		0.08 (4.88)		1	—	UPMA

