



Industrial grade AC locking switches

Product description

Single-pole, double-pole, 3-way, 4-way
 15A, 120/277V/AC; 20A, 120/277V/AC;
 30A, 120/277V/AC



AH1191N



AH1202L

Industrial grade AC Corbin type locking switches, back & side wire



Rating A	V/AC	Description	Catalog no.		
20	120/277	Single-pole, Corbin locking switch	☐ AH1191N	•	•
		Single-pole, Corbin locking switch, key removable in "off" position only	☐ AH1191NOF	•	•
		Double-pole, Corbin locking switch	☐ AH1192N	•	•
		3-Way, Corbin locking switch	☐ AH1193N	•	•

AC locking switches, back & side wire



Rating A	V/AC	Description	Catalog no.			
15	120/277	Single-pole, locking switch	☐ AH1201L	•	•	•
		Double-pole, locking switch	☐ AH1202L	•	•	•
		3-Way, locking switch	☐ AH1203L	•	•	•
		4-Way, locking switch	☐ AH1204L	•	•	•
20	120/277	Single-pole, locking switch	☐ AH1221L	•	•	•
		Double-pole, locking switch	☐ AH1222L	•	•	•
		3-Way, locking switch	☐ AH1223L	•	•	•
		4-Way, locking switch	☐ AH1224L	•	•	•
30	120/277	Single-pole, locking switch	☐ 3031L*	•	•	•
		Double-pole, locking switch	☐ 3032L*	•	•	•

* Not Nom cert

Accessories for industrial grade switches

Description	Catalog no.		
Replacement key for Corbin locking switches	☐ AH14	•	
Stainless steel wallplate for Corbin locking switches with "on-off" indicator engraving	☐ AH1187	•	•
Stainless steel wallplate for Corbin locking switches	☐ AH1188	•	•



AH14



AH1187



AH1188

Specification information: 120/277V industrial locking: E-38

Compliances, specifications and availability are subject to change without notice.



Build-to-spec customizable devices - Page E-6



Indicates NAFTA compliant - Page Q-30



RoHS compliant - Page Q-30