



Hart lock industrial grade 50A locking devices

Product description


2-pole, 3-wire grounding
50A, 250V/DC / 600V/AC
Non-NEMA



3763



3771



3767

Industrial grade plugs & connectors

A	Rating		Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
	V/DC	V/AC							
50	250	600	Pro grip nylon	0.44-1.06" (11.1-26.0mm)	RD & BK	□3763EX	□3762EX		
			Armored	0.68-1.13" (17.3-28.6mm)	Steel		□3762		
			Armored	0.68-1.13" (17.3-28.6mm)	Steel	□3763			

Industrial grade receptacles

A	Rating		Description	Color	Single receptacle		
	V/DC	V/AC					
50	250	600	Industrial receptacles	BK	□3771		

Industrial grade flanged inlets

A	Rating		Description	Color	Flanged inlet	Flanged inlet w/ lid		
	V/DC	V/AC						
50	250	600	Industrial flanged inlets	Steel	□3777	□3767		

Accessories for 50A industrial grade locking devices

Description	Color suffix	Catalog no.		
Weather protective glass-filled nylon, w/ lift lid cover	BK, CR, GY	□7788__		
Weather protective diecast aluminum, w/ lift lid cover		□7770		
Weather protective boot for 50A armored plug		□7716		
Weather protective boot for 50A armored connector		□7717		
Weather protective boot for 50A pro grip plug		□7716EX		
Weather protective boot for 50A pro grip connector		□7717EX		



7788CR
Corrosion resistant



7770



7716



7717



7716EX



7717EX

Dimensional information:
C-80, C-81

Plug & connector specification information:
50A pro grip: C-92
50A armored: C-92
Receptacle specification information:
50A: C-92
Flanged inlet & flanged outlet specification information:
50A: C-92

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BK (Black), GY (Gray), RD (Red), Y or CR (Yellow)



Compliances, specifications and availability are subject to change without notice.