


# Hart lock locking devices

## Hart lock complex environment locking devices

### Product description

3-pole, 3-wire non-grounding  
20A, 125/250V/AC  
NEMA L10-20



**L10-20R**    **L10-20P**



L1020CY



L1120PW

### Hart lock plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	125/ 250	L10-20	Watertight	0.43-1.15" (10.9-29.2mm)	Y	<input type="checkbox"/> L1020PW	<input type="checkbox"/> L1020CW		
			Watertight	0.43-1.15" (10.9-29.2mm)	BK	<input type="checkbox"/> L1020PWBK	<input type="checkbox"/> L1020CWBK		
			Severe duty	0.38-1.00" (9.5-25.4mm)	Y & BK	<input type="checkbox"/> L1020PY	<input type="checkbox"/> L1020CY		

### Hart lock receptacles




Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	
20	125/ 250	L10-20	Watertight	Y	<input type="checkbox"/> L1020RW	
			Watertight	BK	<input type="checkbox"/> L1020RWBK	

## Hart lock complex environment locking devices

### Product description

3-pole, 3-wire non-grounding  
20A, 3Ø 250V/AC  
NEMA L11-20



**L11-20R**    **L11-20P**

### Hart lock 3Ø plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	250	L11-20	3Ø watertight	0.43-1.15" (10.9-29.2mm)	Y	<input type="checkbox"/> L1120PW	<input type="checkbox"/> L1120CW		
			3Ø watertight	0.43-1.15" (10.9-29.2mm)	BK	<input type="checkbox"/> L1120PWBK	<input type="checkbox"/> L1120CWBK		
			3Ø severe duty	0.38-1.00" (9.5-25.4mm)	Y & BK	<input type="checkbox"/> L1120PY	<input type="checkbox"/> L1120CY		

### Hart lock 3Ø receptacles



Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	
20	250	L11-20	3Ø watertight	Y	<input type="checkbox"/> L1120RW	
			3Ø watertight	BK	<input type="checkbox"/> L1120RWBK	

**Dimensional information:**  
D-34-35

**Specification information:**  
Watertight industrial plugs & connectors: D-38  
Watertight industrial receptacles: D-39  
Severe duty industrial plugs & connectors: D-40

### Color information:

BK (Black), Y (Yellow)



**Compliances, specifications and availability are subject to change without notice.**